

Threads "No Go" plug gauge, Thread: M48



Order data

Order number	486030 M48
GTIN	4045197213150
Item class	48B

Description

Version:

The ground first thread pitch removes coarse swarf in the component and prevents premature fracture of the first thread pitch. Version to DIN 2279 - 2299.

"Go" and "No Go" gauges are separate (DIN 2240, part 2, form GE).

Application:

For metric ISO threads, right-hand DIN 13.

Tolerance class 6H (up to M 1.4 = 5H).

Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

Note:

Thread gauges for threads with other pitches, Whitworth, trapezoidal, round, UNC, UNF, NPT, and LH threads available on request.

Technical description

Tolerance class	6H
Thread pitch	5 mm
Thread	M48
Standard	DIN 13
Thread type	M
Tolerance zone	H
Quality	6

Type of gauge	"No Go" gauge
Calibration	L11
Type of product	Thread NoGo plug gauge

Services

DAkkS calibration "Go" / "No Go" thread plug gauge maximum \varnothing 90 mm	028540 90
Calibration "Go" / "No Go" thread plug gauge maximum \varnothing 60 mm	028500 60