



## Machine tap extra long HSS-E-PM 6HX, TiCN, M: M5



### Order data

Order number	134666 M5
GTIN	4045197857507
Item class	11H

### Description

#### Version:

≤ M10: Shank to DIN 371;

≥ M12: Shank to DIN 376.

**With extra long shank.**

**With TiCN coating**, for materials of high hardness and toughness.

#### Advantage:

Designed **for tapping threads where access is difficult.**

Thread type: M

Tool material: HSS E PM

Norm: Manufacturer's standard

Tolerance class: ISO 2X 6HX

Thread pitch: 0.8 mm

Overall length  $L_{tot}$ : 140 mm

Shank Ø: 6 mm

Shank square: 4.9 mm

Tapping hole Ø: 4.2 mm

### Technical description

Thread Ø	5 mm
Taper lead angle	50 degrees
Overall length $L_{tot}$	140 mm
Tolerance class	ISO 2X 6HX
Shank Ø	6 mm
Tapping hole Ø	4.2 mm

Number of clamping slots	3
Norm	Manufacturer's standard
Tool material	HSS E PM
Number of cutting edges Z	3
Shank square	4.9 mm
Thread pitch	0.8 mm
Thread depth	15 mm
Thread type	M
Thread size	M5
Coating	TiCN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Helix angle	45 degrees
Skaft	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue