


**Abrasive sleeve holder, slit, shank  $\varnothing$  6 mm, Head  $\varnothing$ ×head length: 10X20mm****Order data**

Order number	553600 10X20
GTIN	4045197524706
Item class	52E

**Description****Version:**

Slotted, resilient rubber body with steel shank. Ground outer face for best concentricity.

**Technical description**

minimum speed	38000 min <sup>-1</sup>
maximum speed	55000 min <sup>-1</sup>
Head $\varnothing$	10 mm
Head length	20 mm
Shape description	cylindrical
Shank $\varnothing$	6 mm
Backing material	resilient rubber body
Type of product	Tool sleeve carrier