



Burr Tooth configuration STEEL – coarse, Carbide, Type: D0807



Order data

Order number	547100 D0807
GTIN	4007220936849
Item class	55F

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Shank Ø: 6 mm

Shape description: ball

Head Ø: 8 mm

Head length: 7 mm

Overall length: 47 mm

Shank Ø: 6 mm

Technical description

Overall length	47 mm
Head Ø	8 mm
Shape description	ball
Toothing grit designation	coarse
Tooth type abbreviation	STEEL
Shape	D0807
Shank Ø	6 mm
Head length	7 mm

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		