




**Abrasive sleeve holder, slit, shank  $\varnothing$  6 mm, Head  $\varnothing$ ×head length: 22X20mm**



## Order data

Order number	553600 22X20
GTIN	4045197240187
Item class	52E

## Description

### Version:

Slotted, resilient rubber body with steel shank. Ground outer face for best concentricity.

## Technical description

maximum speed	26000 min <sup>-1</sup>
minimum speed	18000 min <sup>-1</sup>
Head $\varnothing$	22 mm
Head length	20 mm
Shape description	cylindrical
Shank $\varnothing$	6 mm
Backing material	resilient rubber body
Type of product	Tool sleeve carrier