



Burr Tooth configuration STEEL – coarse, Carbide, Type: A0616



Order data

Order number	547100 A0616
GTIN	4007220937198
Item class	55F

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Shank Ø: 6 mm

Shape description: Cylindrical

Head Ø: 6 mm

Head length: 16 mm

Overall length: 55 mm

Shank Ø: 6 mm

Technical description

Tooth type abbreviation	STEEL
Overall length	55 mm
Shape description	Cylindrical
Toothing grit designation	coarse
Head Ø	6 mm
Shape	A0616
Shank Ø	6 mm
Head length	16 mm

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		