## 釁 PFERD

# **Burr Tooth configuration STEEL – coarse, Carbide, Type: D1210**



## **Order data**

Order number	547100 D1210		
GTIN	4007220936870		
Item class	55F		

# **Description**

#### **Version:**

**The innovative tooth geometry** permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy.** The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

### **Application:**

Optimised for use on steel and steel castings.

Shank Ø: 6 mm

Shape description: ball

Head Ø: 12 mm Head length: 10 mm Overall length: 51 mm

Shank Ø: 6 mm

# **Technical description**

Shape description	ball		
Tooth type abbreviation	STEEL		
Overall length	51 mm		
Toothing grit designation	coarse		
Shape	D1210		
Head Ø	12 mm		
Shank Ø	6 mm		
Head length	10 mm		

Tool material	Carbide	
Type of product	Burr	

# **User data**

	Suitability	$\mathbf{V}_{c}$	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		