

HOLEX®
Flap disc (ZA) glass fibre pad flat, 178 mm Ø, Grit: 80
Order data

| | |
|--------------|---------------|
| Order number | 565720 80 |
| GTIN | 4045197157980 |
| Item class | 52M |

Description
Version:

Roughing grinding discs with cloth flaps coating with Zirconium Aluminium Oxide (ZA) or ceramic grit on backing pads of steel, plastic or glass fibre. Circumferential speed **ideally 50-60 m/s**, max. 80 m/s. Gentle, cool grinding with high self-sharpening effect (no clogging); low vibration and low force working, low noise level.

· **Flat shape – for surface grinding – and weld dressing with approach angles 0 -15°.**

Flap disc with glass fibre pad and mixed fabric with high metal removal rate and long service life.

Application:

Universal for **all steels**, preferably for use on **flat surfaces**.

Grinding medium code: ZA

Iron, sulphur and chlorine constituents: < 0.1 %

optimised for material: Steel

optimised for material: INOX

maximum circumferential speed: 80 m/s

Shape description: flat

Bore Ø: 22.23 mm

Technical description

| | |
|-----------------------------------|---------|
| recommended approach angle | degrees |
| Grit structure | |
| abrasive, cooling coating | |
| Bonding | |
| Shape | |
| recommended circumferential speed | m/s |
| Backing pad | |

| | |
|---|----------|
| optimised for material | Steel |
| optimised for material | INOX |
| Propulsive equipment | |
| suitable for quick-change system | |
| maximum circumferential speed | 80 m/s |
| Adapter | |
| Grinding media | |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Grinding media backing | |
| See-through grinding | |
| Grinding medium code | ZA |
| Thread | |
| Product name attribute | 178 mm Ø |
| maximum speed | rpm |
| Type of product | |