



Burr Tooth configuration STEEL – coarse, Carbide, Type: A1020



Order data

Order number	547100 A1020
GTIN	4007220937235
Item class	55F

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Shank Ø: 6 mm

Shape description: Cylindrical

Head Ø: 10 mm

Head length: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

Technical description

Overall length	60 mm
Head Ø	10 mm
Tooth type abbreviation	STEEL
Shape description	Cylindrical
Shape	A1020
Toothing grit designation	coarse
Shank Ø	6 mm
Head length	20 mm

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		