

**Garant**
**Solid carbide ball nose slot drill 260°, TiAlN, Ø DC: 10mm**

**Order data**

Order number	207176 10
GTIN	4045197858382
Item class	11X

**Description**
**Version:**

Exact **radius form without profile distortion.**

Double relief ground side clearance angle.

Tolerance: Radius contour = **±0.01 mm.**

With enclosed angle **260°**. Size nominal Ø: **D<sub>c</sub> = -0.01 / -0.025 mm.**

**Note:**

Ground recess after cutter length L<sub>c</sub> is conically increasing.

**Technical description**

Overhang length L <sub>1</sub> incl. recess	50 mm
Recess Ø D <sub>1</sub>	7.1 mm
Shank Ø D <sub>s</sub>	10 mm
Cutting edge Ø D <sub>c</sub>	10 mm
Overall length L	120 mm
Cutter length l <sub>c</sub>	8.7 mm
Feed f <sub>z</sub> for copy milling in steel < 1100 N/mm <sup>2</sup>	0.062 mm
No. of teeth Z	2
Helix angle	30 degrees
Radius R	5 mm
Coating	TiAlN
Tool material	Solid carbide

Standard	Manufacturer's standard
Type	H
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	$0.03 \times D$ for copy milling
Shank	DIN 6535 HA to h5
Through-coolant	no
Colour ring	without
Type of product	Ball-nosed slot drill

### User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	575 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	390 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	390 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	280 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	200 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	200 m/min	M
GG(G)	suitable	575 m/min	K
Uni	suitable		
wet maximum	Suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	Suitable		

### Services

Shank grinding Type HB	129100 HB
------------------------	-----------