



Burr Tooth configuration STEEL – coarse, Carbide, Type: A1225



Order data

Order number	547100 A1225
GTIN	4007220937242
Item class	55F

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Shank Ø: 6 mm

Shape description: cylindrical

Head Ø: 12 mm

Head length: 25 mm

Overall length: 65 mm

Shank Ø: 6 mm

Technical description

Shape	A1225
Overall length	65 mm
Shape description	cylindrical
Tooth type abbreviation	STEEL
Toothing grit designation	coarse
Head Ø	12 mm
Shank Ø	6 mm
Head length	25 mm

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		