


**HOLEX****Abrasive sleeve (ZA) 80 grit medium, Sleeve Ø×Width of sleeve: 22X20mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 553780 22X20  |
| GTIN         | 4045197240514 |
| Item class   | 52E           |

**Description****Version:**

**The rubber body of the abrasive sleeve holder expands at high speed to hold the abrasive sleeve in place.** The full width of the sleeve can be used, it does not slip and can be replaced quickly and easily (twist in the direction of slots when fitting/removing). Only compatible with abrasive sleeve holders.

Made of non-tearing, synthetic resin bonded material with long service life and good grit adhesion. Unsuitable for use with cooling lubricants.

**Zirconium Aluminium Oxide (ZA).****Application:**

Abrasive sleeves are predominantly used for surface grinding tasks which require the removal of large amounts of material – even at sharp edges.

**Suitable for:**

Abrasive sleeve holder No. 553600.

**Technical description**

|              |       |
|--------------|-------|
| Sleeve Ø     | 22 mm |
| Sleeve width | 20 mm |
| Grit         | 80    |

|                      |                           |
|----------------------|---------------------------|
| Grit designation     | medium                    |
| Grinding media       | Zirconium aluminium oxide |
| Grinding medium code | ZA                        |
| Sleeve shape         | cylindrical               |
| Type of product      | Abrasive sleeve           |

### User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable only under restricted conditions |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| GG(G)                          | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |

### Accessories

Abrasive sleeve holder, slit, shank Ø 6 mm Head Ø×head length 22X20 mm

553600 22X20