

Garant
Solid carbide milling cutter MTC, DLC, Ø h6 DC: 16mm

Order data

Order number	202273 16
GTIN	4045197860194
Item class	11X

Description
Version:

With the latest generation of **DLC coating sp²**.

Eccentric relief ground, additionally **polish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium components.

Without 45° cutting edge chamfer.

Application:

Especially for **MTC (Multi Task Cutting)** use on the new generation of turning / milling centres.

Technical description

Shank Ø D _s	16 mm
Feed f _z for slot milling in short-chipping aluminium	0.065 mm
Flute length L _c	36 mm
Overall length L	108 mm
No. of teeth Z	3
Balance quality with shank	G 2.5 with HB
Overhang length L ₁ incl. recess	58 mm
Feed f _z for side milling in short-chipping aluminium	0.09 mm
Recess Ø D ₁	15 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6

Shank form	HB
Tolerance nominal \varnothing	h6
Cutting edge $\varnothing D_c$	16 mm
Helix angle	45 degrees
Corner chamfer angle	90 degrees
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.5 \times D$ for side milling
Through-coolant	no
Machining strategy	MTC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	480 m/min	N
Aluminium (short chipping)	suitable	440 m/min	N
Alu > 10% Si	suitable	400 m/min	N
PMMA acrylic	suitable	200 m/min	N
PE-HD	Suitable	160 m/min	N
PA 66	Suitable	200 m/min	N
PEEK	suitable	150 m/min	N
PF 31	Suitable	130 m/min	N
PVDF GF20	suitable	180 m/min	N

POM GF25	Suitable	160 m/min	N
PA 66 GF30	suitable	150 m/min	N
PEEK GF30	suitable	130 m/min	N
PTFE CF25	suitable	160 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	300 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		