

**XF 870 fibre disc (CER), Ø 125 mm, Grit: 80****Order data**

Order number	566560 80
GTIN	4018875312681
Item class	56V

Description**Version:**

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots. **VSM XF 870** fibre disc with **very high and aggressive cutting performance**, also outstanding working life. Cool grinding. Highly suitable for all steels, high temperature Ni alloys and CrNi steels.

Grit type: **Ceramic grit with cooling, active coating (TOP SIZE)**.

Application:

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 6670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

Technical description

Grit	80
Disc Ø	125 mm
Series	XF870
Grinding media	Ceramic grit with cooling, active coating (TOP SIZE).

Grinding medium code	Ceramic
Grinding media backing	Fibre disc
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
Bore Ø	22.23 mm
optimised for material	Steel
optimised for material	INOX
maximum circumferential speed	80 m/s
maximum speed	12200 min ⁻¹
Type of product	Fibre disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
dry	suitable		

Accessories

Backing padhard/ribbed External Ø 125 mm	566672 125
ISO backing padmedium hard/ribbed External Ø 117 mm	566670 117
ISO backing padflexible/smooth External Ø 117 mm	566650 117