



GARANT Power Tang 90° tangential high-performance shoulder milling cutter, with bore, Ø D / number of effective cutting edges Z: 40/4_ mm

Order data

Order number	215122 40/4_
GTIN	4045197861160
Item class	210

Description

Version:

Maximum stability due to tangentially arranged inserts.
High feed rate values for maximum metal removal rate due to optimum indexable insert with stability in the direction of the cutting force.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.0** with bit No. **674252 size 15IP**.

Setting angle κ : 90 degrees

Milling application: Corner milling

Spacing of the milling cutter's cutting edges: unequal spacing

Through-coolant: Yes

Tool exchange: PowerCard

Technical description

Shank type	with bore
Through-coolant	yes
Setting angle κ	90 degrees
Milling application	Corner milling
Tool exchange	PowerCard
Machining strategy	
Spacing of the cutters	unequal spacing
Type	
Norm	
Type of product	

