



KF 708 fibre disc fused aluminium oxide (A), Ø 180 mm, Grit: 24

Order data

| | |
|--------------|---------------|
| Order number | 566600 24 |
| GTIN | 4018875278673 |
| Item class | 56V |

Description
Version:

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots.

VSM KF 708 high-quality universal fibre disc for grinding metals, plastic, wood etc. Grit type: **Fused aluminium oxide (A)**.

Application:

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 566670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

Technical description

| | |
|----------------------------|---------------------------|
| Grit | 24 |
| Manufacturer's designation | VSM KF 708 |
| Disc Ø | 180 mm |
| Series | KF708 |
| Grinding media | Fused aluminium oxide (A) |
| Grinding medium code | A |
| Grinding media backing | Vulcanised fibre |

| | |
|---|----------------------------|
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 180 mm |
| Adapter | Roloc™ quick-change system |
| Bore Ø | 22.23 mm |
| suitable for quick-change system | Roloc™ |
| optimised for material | Steel |
| maximum circumferential speed | 80 m/s |
| maximum speed | 8488 min ⁻¹ |
| Type of product | Fibre disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| dry | suitable | | |

Accessories

| | |
|---|------------|
| ISO backing padflexible/smooth External Ø 172 mm | 566650 172 |
| Backing padhard/ribbed External Ø 180 mm | 566672 180 |
| ISO backing padmedium hard/ribbed External Ø 172 mm | 566670 172 |