



## Power Tang 90° high performance tangential shoulder milling cutter, with bore, Ø D / Zeff: 50/3\_ mm

### Order data

Order number	215126 50/3_
GTIN	4045197861283
Item class	210

### Description

#### Version:

Maximum stability due to tangentially arranged inserts.

High feed rate values for maximum metal removal rate due to optimum indexable insert with stability in the direction of the cutting force.

#### Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.0** with bit No. **674252 size 15IP**.

Setting angle  $\kappa$ : 90 degrees

Milling application: Corner milling

Spacing of the milling cutter's cutting edges: unequal spacing

Through-coolant: Yes

Tool exchange: PowerCard

### Technical description

Milling application	Corner milling
Through-coolant	yes
Machining strategy	
Shank type	with bore
Setting angle $\kappa$	90 degrees
Spacing of the cutters	unequal spacing
Tool material	
Coating	
Type	
Norm	

Tool exchange

PowerCard

Type of product