

Garant
Clamp toolholder, right-hand, Shank / insert size: 32/19mm

Order data

Order number	250006 32/19
GTIN	4045197861580
Item class	21T

Technical description

ISO code toolholder	MCLNR/L 3232P19
Shank size	32 mm
Shim screw	259025 8
Head length L ₁	40 mm
suitable indexable insert	CN.. 1906..
Screw for clamping claw	259021 5
Functional width L ₄	40 mm
Clamping claw	259038 5
Insert size	19 mm
Shim	259031 24
Overall length L	170 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

8 mm blade with magnetwith 1/4 inch bit holder overall length 50 mm	659874 50
Clamping claw Type 5	259038 5
Screw for clamping claw Type 5	259021 5
Shim screw Type 8	259025 8
Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Shim Type 24	259031 24
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX25	674248 TX25
Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600