


**Cupped flap wheel (A), 60 grit, Head Ø×head width: 60X40mm****Order data**

| | |
|--------------|---------------|
| Order number | 555000 60X40 |
| GTIN | 4045197241276 |
| Item class | 52E |

Description**Version:**

Flap strips bonded on to the shank of the tool.

Cup shaped strip arrangement around the shank of the tool, with recessed core. Shank Ø 6 mm.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component. Particularly suitable for peripheral and internal face grinding.

Technical description

| | |
|-------------------|--------------------------|
| Head width | 40 mm |
| maximum speed | 12000 min ⁻¹ |
| recommended speed | 8000 min ⁻¹ |
| Grit | 60 |
| Shank Ø | 6 mm |
| Head Ø | 60 mm |
| Grinding media | Aluminium Oxide grit (A) |

| | |
|------------------------|------------|
| Grinding medium code | A |
| Product name attribute | 60 grit |
| Type of product | Flap wheel |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| dry | suitable | | |