

Garant
Lever lock toolholder, right-hand, Shank / insert size: 20/15mm

Order data

Order number	250612 20/15
GTIN	4045197861733
Item class	21T

Technical description

Functional width L ₄	12 mm
Head length L ₁	35 mm
Lever	259015 8
Shim	259031 28
suitable indexable insert	DN.. 1506..
Shim punches pack	259047 2
Shim pins pack	259044 2
Overall length L	125 mm
ISO code toolholder	PDNNR/L 2020K15
Insert size	15 mm
Shank size	20 mm
Lever screw	259018 7
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	63 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 8	259015 8
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2
Lever screw Type 7	259018 7
Shim Type 28	259031 28
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500