

HOLEX**Abrasive strip wheel (A), Ø 165 × 30 mm, Grit: 80****Order data**

| | |
|--------------|---------------|
| Order number | 555145 80 |
| GTIN | 4045197525673 |
| Item class | 52E |

Description**Version:**

Abrasive strip wheels with **Aluminium Oxide (A)**. Bore Ø 54 mm.

Application:

Removing and cleaning up weld seams, grinding large areas, and workpieces that have an irregular profile.

Note:

For mounting on shafts smaller than Ø 54 mm, use the metal flange No. 555140, which can be bored out to suit. Other sizes available on request.

Technical description

| | |
|----------------------|------------------------------|
| Bore Ø | 54 mm |
| Grit | 80 |
| Grinding media | Standard aluminium oxide (A) |
| Grinding medium code | A |
| Disc Ø | 165 mm |

| | |
|------------------------|------------------------|
| Disc thickness | 30 mm |
| Product name attribute | Ø 165 × 30 mm |
| maximum speed | 5200 min ⁻¹ |
| Type of product | Abrasive strip wheel |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable only under restricted conditions | | |
| Stone | suitable only under restricted conditions | | |
| Paint | suitable | | |
| Uni | suitable | | |
| dry | suitable | | |

Accessories

555140 54

Metal reducing flange pair, can be bored out suitable for
bore \varnothing 54 mm
