



Coarse cleaning disc (SiC), CG-RD, Disc Ø: 115mm



Order data

Order number	566715 115
GTIN	40467197510510
Item class	53M

Description

Version:

Cleaning discs with synthetic nylon fleece evenly impregnated with abrasive grit on glass fibre pad.

Very **coarse non-woven abrasive mesh structure**, will not clog even when used on soft thick coatings.

Flexible fleece body, ideal for **grinding convex surfaces**. Creates a soft and even finish, especially suitable for visible surfaces.

Application:

For rust removal, paint removal, dressing weld seams and removing surface dirt.

With **glass fibre backing pad for direct clamping** on angle grinders.

Note:

For deburring wheels for double-ended bench grinding machines, see No. 556270 onwards.

Technical description

maximum speed	11000 min ⁻¹
recommended speed	5000 - 7000 min ⁻¹
Bore Ø	22.23 mm
Disc Ø	115 mm

Grinding medium code	SiC
Degree of hardness	medium
Grit designation	very coarse
Iron, sulphur and chlorine constituents	< 0.1 %
Shape description	flat
Product name attribute	CG-RD
maximum circumferential speed	60 m/s
Type of product	Rough cleaning non-woven abrasive mesh

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		

