



Coarse cleaning disc (SiC), Disc Ø: 125mm



Order data

| | |
|--------------|---------------|
| Order number | 566750 125 |
| GTIN | 4045197566133 |
| Item class | 52E |

Description

Version:

Cleaning discs with synthetic nylon fleece evenly impregnated with abrasive grit on glass fibre pad.

Very **coarse non-woven abrasive mesh structure**, will not clog even when used on soft thick coatings.

Hard and aggressive fleece body for **general-purpose use** on large areas.

Application:

For rust removal, paint removal, dressing weld seams and removing surface dirt.

With **glass fibre backing pad for direct clamping** on angle grinders.

Note:

For deburring wheels for double-ended bench grinding machines, see No. 556270 onwards.

Technical description

| | |
|-------------------|-------------------------------|
| recommended speed | 5000 - 7000 min ⁻¹ |
| maximum speed | 10000 min ⁻¹ |
| Bore Ø | 22.23 mm |
| Disc Ø | 125 mm |

| | |
|-----------------------------------------|----------------------------------------|
| Grinding medium code | SiC |
| Degree of hardness | hard |
| Grit designation | very coarse |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Shape description | flat |
| maximum circumferential speed | 60 m/s |
| Type of product | Rough cleaning non-woven abrasive mesh |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|-------------------------------------------|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable | | |
| Uni | suitable | | |
| wet maximum | suitable only under restricted conditions | | |
| dry | suitable | | |

