

ALLURIS

FMI-S10 Digital force gauge (solar), Measuring range: 100N**Order data**

Order number	478980 100
GTIN	4260244680369
Item class	47F

Description**Version:**

- **Sturdy force gauges in a handy aluminium die-cast housing for compressive and tensile forces from 0.001 to 2500 N.**
- **Overload protection up to 500% and protected measurement shaft.**
- **Attachment thread for additional handles.**
- **Precise positioning in test stands by a guide pin.**
- **Ready for use at all times thanks to the free-standing photo-voltaic power supply.**

Function:

IP40: Protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away, and offers no protection against water.

Application:

Measurement of compressive and tensile forces in quality assessment and production. For use as a mobile manual measurement gauge both in outdoor areas and in test stands or jigs. Attachment thread integrated into the housing permit attachment in test stands or mounting of additional handles.

Supplied with:

Force gauge in a protective case. Screw-on accessories for force transfer (flat head, slot head, cone, hook). Quick-start instructions.

Technical description

IP Index of Protection	IP 40
Measuring range	100 N
Resolution	0.1 N
Width	82 mm
Height	29 mm
Length	150 mm
Error limit	±0.3 maximum value (±1 digit) %
Connection thread	M6
Power supply	solar-powered
Measurement technology	digital
Calibration	Price on request
Type of product	Draw bar pulling force gauge