

**Flap disc (special ZA) glass fibre pad flat, 115 mm Ø, Grit: 40****Order data**

Order number	565300 40
GTIN	4045197157768
Item class	51M

**Description****Version:**

Roughing grinding discs with cloth flaps coating with Zirconium Aluminium Oxide (ZA) or ceramic grit on backing pads of steel, plastic or glass fibre. Circumferential speed **ideally 50-60 m/s**, max. 80 m/s. Gentle, cool grinding with high self-sharpening effect (no clogging); low vibration and low force working, low noise level.

· **Flat shape – for surface grinding – and weld dressing with approach angles 0 -15°.**

Flap disc with glass fibre pad and polyester fabric with greatly above-average working life.

**Application:**

Universal for **all steels**, even for use on **hardened edges**.

Grinding medium code: ZA

Iron, sulphur and chlorine constituents: < 0.1 %

optimised for material: Steel

optimised for material: INOX

maximum circumferential speed: 80 m/s

Shape description: flat

Bore Ø: 22.23 mm

**Technical description**

Bore Ø	22.23 mm
Shape description	flat
Grit	40
Disc Ø	115 mm
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	115 mm Ø
optimised for material	Steel
optimised for material	INOX
maximum circumferential speed	80 m/s