



## Spring balance, maximum measuring range: 10N



### Order data

Order number	478900 10N
GTIN	4045197208149
Item class	42H

### Description

#### Version:

Sturdy metal housing in practical design; hammer finish. Clear dial face with double scale for measuring in both directions. With pointer and memory pointer.

#### Application:

For electrical engineering and fine mechanical work, e.g. setting the contact pressure of relay springs, checking the brush pressure on motors or for adjusting tension or compression springs.

#### Accuracy:

$\pm 0.01 \times (\text{measuring range} + \text{measured value})$ .

Calibration: K1

Measuring range: 1 - 10 N

Scale graduations: 0.2 N

Probe length L: 48 mm

Dial face  $\varnothing$ : 72 mm

### Technical description

Dial face $\varnothing$	72 mm
Probe length L	48 mm
Measuring range	1 - 10 N
Scale graduations	0.2 N
Calibration	K1

Measurement technology	analogue
Type of product	Spring balance

**Services**

Labelling laser-etched Type	018940
Calibration Spring balance	018870
Calibration Spring balance Type F	027730 F