

Garant
CC.T 060204, Grade: HB7035-1


Order data

Order number	260052 HB7035-1
GTIN	4045197873682
Item class	21G

Description

CC.T 060204 HB7035-1 Grade: HB7035-1
 Chip breaker: SS
 Tolerance: M
 Cutting depth a_p : 0.2 - 2.5 mm
 Feed f : 0.05 - 0.25 mm/rev.
 Cutting speed v_c main application: 120 - 350 m/min

Technical description

Cutting conditions	heavily interrupted
Main application	P
Feed f	0.05 - 0.25 mm/rev.
Cutting speed v_c main application	120 - 350 m/min
Corner radius	0.4 mm
Grade	HB7035-1
Cutting depth a_p	0.2 - 2.5 mm

Chip breaker	SS
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 060204
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning