

**Garant**
**Solid carbide slot drill, AlCrN, Ø e8 DC: 20mm**

**Order data**

Order number	201302 20
GTIN	4045197862556
Item class	11X

**Description**
**Version:**

 Dimensions similar to **DIN 6527**.

Improved coating for general-purpose applications in steel and cast iron.

**Technical description**

Direction of infeed	horizontal, oblique and vertical
Feed $f_z$ for side milling in steel $< 750 \text{ N/mm}^2$	0.15 mm
Corner chamfer width at $45^\circ$	0.5 mm
No. of teeth Z	2
Shank $\varnothing D_s$	20 mm
Tolerance nominal $\varnothing$	e8
Feed $f_z$ for slot milling in steel $< 750 \text{ N/mm}^2$	0.1 mm
Shank	DIN 6535 HB to h6
Flute length $L_c$	26 mm
Shank form	HB
Cutting edge $\varnothing D_c$	20 mm
Overall length L	92 mm
Helix angle	30 degrees
Corner chamfer angle	45 degrees

Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Alu > 10% Si	suitable only under restricted conditions	200 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	70 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	50 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

dry	suitable only under restricted conditions
Air	suitable