

Garant**DNMG 110408, Grade: HB7035-1**

Order data

Order number	250754 HB7035-1
GTIN	4045197874221
Item class	21G

Description

DNMG 110408 HB7035-1 Grade: HB7035-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 5 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 100 - 320 m/min

Technical description

Feed f	0.2 - 0.5 mm/rev.
Chip breaker	SM
Cutting speed v_c main application	100 - 320 m/min
Cutting conditions	heavily interrupted
Main application	P
Grade	HB7035-1

Cutting depth a_p	0.5 - 5 mm
Corner radius	0.8 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	DNMG 110408
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning