

Garant
KNUX 160410R, Grade: HB7035-1

Order data

Order number	251036 HB7035-1
GTIN	4045197874344
Item class	21G

Description

KNUX 160410R HB7035-1 Grade: HB7035-1
 Chip breaker: SM
 Chip diverter: 2.2 mm
 Cutting depth a_p : 0.5 - 5 mm
 Feed f : 0.2 - 0.5 mm/rev.
 Cutting speed v_c main application: 100 - 320 m/min

Technical description

Corner radius	1 mm
Grade	HB7035-1
Feed f	0.2 - 0.5 mm/rev.
Main application	P
Chip diverter	2.2 mm
Cutting conditions	heavily interrupted
Cutting depth a_p	0.5 - 5 mm
Chip breaker	SM
Cutting speed v_c main application	100 - 320 m/min
Finishing/roughing assignment	Semi-roughing

Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160410R
Type of product	Indexable insert for turning