

Garant**RC.X 1204, Grade: HB7035-1**

Order data

Order number	260650 HB7035-1
GTIN	4045197874399
Item class	21G

Description

RC.X 1204 HB7035-1 Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 2 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 100 - 320 m/min

Technical description

Grade	HB7035-1
Main application	P
Cutting speed v_c main application	100 - 320 m/min
Chip breaker	SM
Cutting depth a_p	0.5 - 2 mm
Feed f	0.1 - 0.3 mm/rev.
Cutting conditions	heavily interrupted

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	RCMX 1204
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning