

Garant**SNMG 120408, Grade: HB7035-1****Order data**

Order number	251224 HB7035-1
GTIN	4045197874498
Item class	21G

Description

SNMG 120408 HB7035-1 Corner radius: 0.8 mm
Grade: HB7035-1
Chip breaker: SM
Cutting depth a_p : 0.5 - 6 mm
Feed f : 0.15 - 0.5 mm/rev.
Cutting speed v_c main application: 100 - 320 m/min

Technical description

Chip breaker	SM
Cutting conditions	heavily interrupted
Cutting depth a_p	0.5 - 6 mm
Grade	HB7035-1
Corner radius	0.8 mm
Main application	P
Cutting speed v_c main application	100 - 320 m/min

Feed f	0.15 - 0.5 mm/rev.
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Type of product	Indexable insert for turning