

Garant
Solid carbide milling cutter, AlCrN, Ø e8 DC: 1,1mm

Order data

Order number	201308 1,1
GTIN	4045197863140
Item class	11X

Description
Version:

Dimensions similar to **DIN 6527**.

Improved coating for general-purpose applications in steel and cast iron.

Note:

Successor product for No. 201630 and 201522.

Technical description

Shank	DIN 6535 HA to h6
Cutting edge Ø D _c	1.1 mm
Corner chamfer width at 45°	0.1 mm
Overall length L	50 mm
Shank form	HA
Feed f _z for side milling in steel < 750 N/mm ²	0.006 mm
Direction of infeed	horizontal, oblique and vertical
No. of teeth Z	2
Feed f _z for slot milling in steel < 750 N/mm ²	0.005 mm
Tolerance nominal Ø	e8
Flute length L _c	3 mm
Shank Ø D _s	3 mm
Helix angle	30 degrees

Corner chamfer angle	45 degrees
Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	0.3xD for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1xD
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Alu > 10% Si	suitable only under restricted conditions	200 m/min	N
Steel < 500 N/mm ²	suitable	120 m/min	P
Steel < 750 N/mm ²	suitable	110 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	60 m/min	P
INOX < 900 N/mm ²	suitable	70 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	50 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

dry	suitable only under restricted conditions
Air	suitable