

Garant
SNMG 190612, Grade: HB7035-1


Order data

Order number	251236 HB7035-1
GTIN	4045197874573
Item class	21G

Description

SNMG 190612 HB7035-1 Corner radius: 1.2 mm
 Grade: HB7035-1
 Chip breaker: SM
 Cutting depth a_p : 0.5 - 6 mm
 Feed f : 0.15 - 0.5 mm/rev.
 Cutting speed v_c main application: 100 - 320 m/min

Technical description

Cutting depth a_p	0.5 - 6 mm
Feed f	0.15 - 0.5 mm/rev.
Corner radius	1.2 mm
Main application	P
Cutting speed v_c main application	100 - 320 m/min
Cutting conditions	heavily interrupted
Grade	HB7035-1

Chip breaker	SM
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 190612
Number of changes/inserts	8
Type of product	Indexable insert for turning