

Garant
VB.T 160404, Grade: HB7035-1


Order data

Order number	261232 HB7035-1
GTIN	4045197874825
Item class	21G

Description

VB.T 160404 HB7035-1 Grade: HB7035-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 2.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 100 - 320 m/min

Technical description

Corner radius	0.4 mm
Main application	P
Chip breaker	SM
Cutting conditions	heavily interrupted
Cutting speed v_c main application	100 - 320 m/min
Grade	HB7035-1
Cutting depth a_p	0.5 - 2.5 mm

Feed f	0.1 - 0.3 mm/rev.
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	VBMT 160404
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning