

Garant
VBMT 160408, Grade: HB7035-1


Order data

| | |
|--------------|-----------------|
| Order number | 261154 HB7035-1 |
| GTIN | 4045197874832 |
| Item class | 21G |

Description

VBMT 160408 HB7035-1 Grade: HB7035-1
 Chip breaker: SS
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.05 - 0.2 mm/rev.
 Cutting speed v_c main application: 120 - 350 m/min

Technical description

| | |
|--------------------------------------|---------------------|
| Chip breaker | SS |
| Cutting depth a_p | 0.2 - 1.5 mm |
| Main application | P |
| Cutting speed v_c main application | 120 - 350 m/min |
| Cutting conditions | heavily interrupted |
| Corner radius | 0.8 mm |
| Grade | HB7035-1 |

| | |
|-------------------------------|------------------------------|
| Feed f | 0.05 - 0.2 mm/rev. |
| Finishing/roughing assignment | Finishing |
| Tool material | Carbide |
| ISO code indexable insert | VBMT 160408 |
| Number of changes/inserts | 2 |
| Type of product | Indexable insert for turning |