


Garant**WNMG 080412, Grade: HB7035-1**

Order data

Order number	252072 HB7035-1
GTIN	4045197875068
Item class	21G

Description

WNMG 080412 HB7035-1 Grade: HB7035-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 100 - 320 m/min

Technical description

Corner radius	1.2 mm
Cutting speed v_c main application	100 - 320 m/min
Main application	P
Cutting conditions	heavily interrupted
Chip breaker	SM
Feed f	0.2 - 0.5 mm/rev.
Grade	HB7035-1

Cutting depth a_p	0.5 - 4 mm
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	WNMG 080412
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning