

3M Scotch-Brite™

**Abrasive fleece pad, 158×224 mm, Fleece structure: 1000****Order data**

|              |               |
|--------------|---------------|
| Order number | 556000 1000   |
| GTIN         | 3134375235693 |
| Item class   | 53M           |

**Description****Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding.

**Advantage:**

- **Adapts to the shape of the component.**
- **The open structure prevents clogging and reduces heat development.**
- **Consistent reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

**Application:**

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Fine / very fine:** for cleaning delicate surfaces, for removing light scratches on metals. Also suitable for applying fine / very fine matt finishes to steels and non-ferrous metals.

**Technical description**

|   |              |
|---|--------------|
| Grit equivalent                         | 600 - 1000   |
| Colour                                  | grey         |
| Fleece structure                        | 1000         |
| Grit designation                        | very fine    |
| 3M designation                          | CF-HP        |
| Version                                 | S Ultra Fine |
| Iron, sulphur and chlorine constituents | < 0.1 %      |

|                        |                     |
|------------------------|---------------------|
| Width                  | 158 mm              |
| Length                 | 224 mm              |
| Product name attribute | 158x224 mm          |
| Type of product        | Abrasive fleece pad |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable                                  |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable                                  |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Stone                          | suitable only under restricted conditions |                |          |
| Paint                          | suitable                                  |                |          |
| Uni                            | suitable                                  |                |          |
| wet maximum                    | suitable only under restricted conditions |                |          |
| dry                            | suitable                                  |                |          |

## Accessories

|         |        |
|---------|--------|
| Mandrel | 556030 |
|---------|--------|

Hand block

556020