

**Garant**
**Solid carbide mini milling cutter, AlCrN, Ø e8 DC: 6mm**

**Order data**

Order number	202260 6
GTIN	4045197863805
Item class	11X

**Description**
**Version:**

 Shank similar to **DIN 6535 HB**.

Improved coating for general-purpose applications in steel and cast iron.

**Save on regrinding costs:**

It is cheaper to use solid carbide mini milling cutters to the wear limit than to regrind them.

**Technical description**

Feed $f_z$ for slot milling in steel $< 750 \text{ N/mm}^2$	0.04 mm
Overall length L	45 mm
Cutting edge $\varnothing D_c$	6 mm
No. of teeth Z	3
Flute length $L_c$	8 mm
Corner chamfer width at $45^\circ$	0.2 mm
Shank	HB with h6
Feed $f_z$ for side milling in steel $< 750 \text{ N/mm}^2$	0.05 mm
Shank form	HB
Direction of infeed	horizontal, oblique and vertical
Shank $\varnothing D_s$	6 mm
Tolerance nominal $\varnothing$	e8

Helix angle	30 degrees
Corner chamfer angle	45 degrees
Coating	AlCrN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Alu > 10% Si	suitable only under restricted conditions	200 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	70 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	50 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable		
wet maximum	suitable		

wet minimum	suitable
dry	suitable only under restricted conditions
Air	suitable