



## Precision angle bender complete with accessories, maximum component height: 35mm



### Order data

Order number	823600 35
GTIN	2050001932709
Item class	86K

### Description

#### Version:

Easy to operate, powerful bending machine for precise bending of various profiles up to 180°. Positive and secure clamping of the profiles. Good repetition accuracy of the bend thanks to the precise bending and clamping jig. Integral **angle and length stops for quick working** with exact bending results. Smooth operation even with solid profiles due to a **needle-bearing turntable** (size 60 and 100).

#### Application:

Precise and user-friendly hot and cold bending (bending angle 0 – 180°), both with angular bending edges and also with various bending radii.

#### Suitable for:

Vice

#### Supplied with:

1 bending plate, sharp-edged, 90° No. 823601 size 0, 1 bending plate (r = 6 mm), 180°, 1 angle stop, 1 length stop, 1 operating handle, 1 wrench 5 - 6 - 9 - 10 - 17 AF.

#### Note:

Further bending plates can be found under No. 823601 – 823604.

### Technical description

Weight	9.3 kg
Height	92 mm
maximum bending capacity for flat material (hot)	36x6 / 11x11 mm
maximum component height	35 mm

Depth	150 mm
Width	280 mm
maximum bending capacity for flat material (cold)	35×4 / 9×9 mm
maximum bending capacity for round material (cold) Ø	10 mm
Type of product	Bending machine

---

## Accessories

Bending tool Radius 4	823601 4
Bending tool Radius 10	823601 10
Bending tool Radius 0	823601 0
Bending tool Radius 2,5	823601 2,5