



Precision angle bender complete with accessories, maximum component height: 60mm



Order data

Order number	823600 60
GTIN	2050001933065
Item class	86K

Description

Version:

Easy to operate, powerful bending machine for precise bending of various profiles up to 180°. Positive and secure clamping of the profiles. Good repetition accuracy of the bend thanks to the precise bending and clamping jig. Integral **angle and length stops for quick working** with exact bending results. Smooth operation even with solid profiles due to a **needle-bearing turntable** (size 60 and 100).

Application:

Precise and user-friendly hot and cold bending (bending angle 0 – 180°), both with angular bending edges and also with various bending radii.

Suitable for:

Vice / workbench

Supplied with:

1 bending plate (r = 2 mm), 90° No. 823602 size 2, 1 angle stop, 1 length stop, 1 operating handle, 1 cover pin, 1 wrench 5 - 6 - 8 - 10 AF.

Note:

Further bending plates can be found under No. 823601 – 823604.

Technical description

Height	145 mm
maximum bending capacity for round material (cold) Ø	15 mm
maximum bending capacity for flat material (cold)	60×6 / 13×13 mm

Depth	200 mm
maximum component height	60 mm
Width	335 mm
maximum bending capacity for flat material (hot)	60×10 / 20×20 mm
Weight	22.4 kg
Type of product	Bending machine

Accessories

Bending tool Radius 8	823602 8
Bending tool Radius 10	823602 10
Bending tool Radius 2	823602 2
Bending tool Radius 5	823602 5