

Garant
Shrink-fit chuck 3°, extra slim, HSK-E 40 A = 60, Clamping Ø D1: 8 mm

Order data

Order number	308321 8
GTIN	4045197875730
Item class	31A

Description
Version:

- All shanks hard turned (for smooth running!).
- HSK mating faces machined.
- Slim design (3° contour).

Extra-slim style.

Balancing quality 2.5 / 40,000 rpm.
Application:

- Especially in operations in tool and mould making.
- For clamping tools with shank tolerance h6.

Optional extras:

Coolant feed pipe No. 309880. Socket No. 309890. Shrink-fit chuck extensions No. 302410 sizes 12/3 and 12/4. Shrink-fit units No. 354210 – 354450. Balancing screw set No. 309906 180.

Machining strategy: HSC

 Clamping Ø D₁: 8 mm

External Ø D: 15 mm

 Ø D₂: 11 mm

Technical description

Ø D ₂	11 mm
Clamping Ø D ₁	8 mm
External Ø D	15 mm

Adapter	HSK-E 40 A = 60
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	E
Balance quality G at rotational speed	G 2.5 at 40,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Shrink-fit chuck

Accessories

Cooling adapter short4.5° for clamping Ø 6-9 mm	354235 6-9
Cooling adapter long4.5° for clamping Ø 6-9 mm	354236 6-9
Subframe cupboard	354290
Screening plate for coilSU1 for clamping Ø 6-12 mm	354240 6-12
Shrink-fit unit Type SU1	354210 SU1
Cooling unit Type CU1	354215 CU1