

**Garant**
**Through hole taps, stub + tapping drills + tap wrench, for metric threads:  
M3-12**

**Order data**

Order number	146260 M3-12
GTIN	4045197876560
Item class	11K

**Description**
**Version:**

When the case is opened, the tools raise up vertically and can easily be selected.  
Consisting of spiral point taps M3; M4; M5; M6; M8; M10; M12, tapping drills size 2.5; 3.3; 4.2; 5; 6.8; 8.5; 10.2 and tap wrench size 1.1/2.

**Content:**

1 pc. each spiral point tap M3 – M12 No. 131450, tapping drill No. 114150 and tap wrench No. 148410

Standard: DIN 352

**Technical description**

for metric threads	M3 – M12
Thread type	M
Flank angle	60°
Standard	DIN 352
Type of product	Tap

---

**Accessories**

Spiral point tap stub M M8	131450 M8
HSS jobber drill N Ø DC h8 (mm or inch) 10,2	114150 10,2
Spiral point tap stub M M5	131450 M5
HSS jobber drill N Ø DC h8 (mm or inch) 6,8	114150 6,8
HSS jobber drill N Ø DC h8 (mm or inch) 8,5	114150 8,5
HSS jobber drill N Ø DC h8 (mm or inch) 2,5	114150 2,5
Spiral point tap stub M M10	131450 M10
Spiral point tap stub M M3	131450 M3
HSS jobber drill N Ø DC h8 (mm or inch) 4,2	114150 4,2
Tap wrench, adjustable Type 2	148410 2
HSS jobber drill N Ø DC h8 (mm or inch) 5	114150 5
Spiral point tap stub M M4	131450 M4
Spiral point tap stub M M12	131450 M12
HSS jobber drill N Ø DC h8 (mm or inch) 3,3	114150 3,3
Tap wrench, adjustable Type 1.1/2	148410 1.1/2
Spiral point tap stub M M6	131450 M6
Empty case Type 3	146960 3