



## Solid carbide mini milling cutter, uncoated, $\varnothing$ e8 DC: 14mm



### Order data

Order number	202266 14
GTIN	4045197864895
Item class	12X

### Description

#### Version:

Shank similar to **DIN 6535 HB**.

#### Save on regrinding costs:

It is cheaper to use solid carbide mini milling cutters to the wear limit than to regrind them.

### Technical description

Cutting edge $\varnothing D_c$	14 mm
Direction of infeed	horizontal, oblique and vertical
Flute length $L_c$	15 mm
Shank	HB with h6
Tolerance nominal $\varnothing$	e8
Feed $f_z$ for side milling in steel $< 750 \text{ N/mm}^2$	0.1 mm
Shank form	HB
Feed $f_z$ for slot milling in steel $< 750 \text{ N/mm}^2$	0.07 mm
No. of teeth Z	3
Overall length L	60 mm
Shank $\varnothing D_s$	14 mm
Helix angle	45 degrees
Corner chamfer angle	90 degrees

Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	170 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	100 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	45 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	40 m/min	M
GG(G)	suitable only under restricted conditions	55 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	Suitable		
dry	suitable only under restricted conditions		
Air	Suitable		

