

Garant
Burr Z9 very coarse (NF/Alu), Carbide, Type: F0618

Order data

Order number	540709 F0618
GTIN	4045197522528
Item class	51D

Description
Version:

 Shank \varnothing 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round arch shape F** (RBF).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

 Shank \varnothing : 6 mm

Shape description: round arch

 Head \varnothing : 6 mm

Head length: 18 mm

Overall length: 50 mm

 Shank \varnothing : 6 mm

Technical description

Toothing grit designation	very coarse (NF/Alu)
Shape	F0618
Tooth type abbreviation	Z9
Overall length	50 mm
Head \varnothing	6 mm
Shape description	round arch

Shank Ø	6 mm
Head length	18 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		