

## Garant

### Jobber drill long HSS N, uncoated, Ø DC h8: 2mm



#### Order data

Order number	116000 2
GTIN	4045197025227
Item class	11B

#### Description

##### Version:

Vaporised from 2.4 mm. Particularly for deep hole drilling (for deep holes, repeated chip evacuation is necessary).

With point geometry shape A from size 4 mm.

##### Advantage:

Especially suitable for **long reach purposes**. (When used to drill deep holes, low feed rates and frequent drill pecks are necessary).

##### Recommendation:

##### Maximum drilling depth:

$$L_2 = L_C - 1.5 \times D_C$$

##### Note:

Suitable NC spotting drills No. 112103, 112110 and 112160 with **120° tip angle** for enhanced process reliability.

#### Technical description

Number of cutting edges Z	2
Feed f in steel < 750 N/mm <sup>2</sup>	0.02 mm/rev.
Nominal Ø D <sub>C</sub>	2 mm
Flute length L <sub>C</sub>	56 mm
Tolerance nominal Ø	h8
Shank Ø D <sub>S</sub>	2 mm
Overall length L	85 mm
Standard	DIN 340

recommended maximum drilling depth L <sub>2</sub>	53 mm
Point angle	118 degrees
Shank	Plain shank
Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	64 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	52 m/min	N
Alu > 10% Si	suitable only under restricted conditions	40 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
GG(G)	suitable only under restricted conditions	25 m/min	K
Oil	suitable		
wet maximum	suitable		