

**Garant**
**Solid carbide milling cutter, AlCrN, Ø e8 DC: 9,5mm**


## Order data

Order number	202267 9,5
GTIN	4045197865045
Item class	11X

## Description

### Version:

Dimensions similar to **DIN 6527**.

Improved coating for general-purpose applications in steel and cast iron.

## Technical description

Overall length L	72 mm
Direction of infeed	horizontal, oblique and vertical
Tolerance nominal Ø	e8
Recess Ø D <sub>1</sub>	9.3 mm
Flute length L <sub>c</sub>	22 mm
Shank	DIN 6535 HA to h6
Shank Ø D <sub>s</sub>	10 mm
Feed f <sub>z</sub> for slot milling in steel < 750 N/mm <sup>2</sup>	0.05 mm
Feed f <sub>z</sub> for side milling in steel < 750 N/mm <sup>2</sup>	0.08 mm
No. of teeth Z	3
Cutting edge Ø D <sub>c</sub>	9.5 mm
Overhang length L <sub>1</sub> incl. recess	32 mm
Helix angle	30 degrees
Corner chamfer angle	90 degrees

Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Alu > 10% Si	suitable only under restricted conditions	200 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	70 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	50 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

dry	suitable only under restricted conditions
<b>Air Services</b>	suitable
Shank grinding Type HB	129100 HB