



Driven tool, radial, OT rail, VX3, Type: 30-VX3-LIK



Order data

Order number	319959 30-VX3-LIK
GTIN	4045197877260
Item class	31W

Description

Version:

For use on **disc turrets**. Left-hand version, i.e. machining in the direction of the main spindle. Ratio 1:1. Version with internal cooling (internal) max. 70 bar.

For use on all **DMG Gildemeister CTX** CNC lathes with **Sauter** turret. Drive coupling **DIN 5480**.

Clamping of tools in driven tool using ER collet with external nut or VARIA VX quick-change system under license from EWS. External cooling via a coolant tube, internal cooling through the tool centrally through the spindle. Maximum speed 8000 rpm.

OT rail.

Version IKD – with ceramic seal set, pressures up to 70 bar, with full dry-run capability.

Advantage:

- **Weight- and geometry-optimized design.**
- **Process reliability through high-quality components, longevity.**
- **High torque transmission.**
- **100% control – each driven tool is subjected to a run-in programme.**
- **Internal cooling: specially developed and patented seal.**

Application:

As many machining steps as possible in one clamping set-up. Where space (available clamping positions) in the revolver is at a premium.

Suitable for :

DMG Gildemeister CTX. In some cases, Emco, Hardinge, Monforts, Scherer etc. with DIN 5480.

Supplied with:

Driven tool for collet: including clamping nut and hook spanner. Driven tool VARIA VX: including chuck key.

Optional extras:

Suitable inserts, Varia VX No. 319802 – 319888, ER collets No. 308941 – 309878, ER chuck keys No. 309680 – 309745.

Note:

- **Other drive types (such as DIN 5482), ratios, dimensions, BMT etc. on request, see: www.hoffmann.ews-tools.com**
- **IC tools (with through cooling) will not run dry with standard seal, coolant filtering < 50 µm.**
- **Recommendation: Tighten version VARIA VX with a torque tool (max. 6 Nm).**

Tool clamping: Varia VX3

l₁: 134 mm

b₁: 69.5 mm

b₂: 59.5 mm

h₁: 68 mm

x: 100 mm

Cooling: internal

Technical description

Cooling	internal
x	100 mm
l ₁	134 mm
h ₁	68 mm
b ₂	59.5 mm
b ₁	69.5 mm
Adapter	VX3
VDI size	30
Tool clamping	Varia VX3

Accessories

Indexable drill toolholder VARIA VX3 Clamping range Ø
D1 6 mm

319823 6

Indexable drill toolholder VARIA VX3 Clamping range Ø
D1 10 mm

319823 10

Axial milling cutter spigot VARIA VX3 Spigot Ø d1 27 mm	319835 27
Axial milling cutter spigot VARIA VX3 Spigot Ø d1 16 mm	319835 16
Varia collet chuck VARIA VX3 for ER collets 25 ER	319802 25
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 25 mm	319823 25
Varia collet chuck VARIA VX3 for ER collets 32 ER	319802 32
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 16 mm	319823 16
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 12 mm	319823 12
Varia collet chuck VARIA VX3 for ER collets 16 ER	319802 16
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 8 mm	319823 8
Indexable drill toolholder VARIA VX3 Clamping range Ø D1 20 mm	319823 20
Axial milling cutter spigot VARIA VX3 Spigot Ø d1 22 mm	319835 22
Varia collet chuck VARIA VX3 for ER collets 20 ER	319802 20