



Solid carbide end mill, uncoated, Ø e8 DC: 10 mm

Order data

Order number	202276 10
GTIN	4045197865632
Item class	12X

Description
Version:

Dimensions similar to **DIN 6527**.

Through-coolant: no

Tolerance nominal Ø: e8

No. of teeth Z: 3

Helix angle: 30 degrees

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HB to h6

No. of teeth Z: 3

Flute length L_c : 14 mm

Overall length L: 66 mm

Shank Ø D_s : 10 mm

Shank form: HB

Corner chamfer width at 45°: 0.3 mm

Technical description

Tolerance nominal Ø	e8
Corner chamfer width at 45°	0.3 mm
Direction of infeed	horizontal, oblique and vertical
Feed f_z for slot milling in steel < 750 N/mm ²	0.06 mm
Shank form	HB
Shank	DIN 6535 HB to h6
No. of teeth Z	3

Overall length L	66 mm
Cutting edge $\varnothing D_c$	10 mm
Feed f_z for side milling in steel $< 750 \text{ N/mm}^2$	0.09 mm
Flute length L_c	14 mm
Shank $\varnothing D_s$	10 mm
Helix angle	30 degrees
Corner chamfer angle	45 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	without
Type of product	End mill