

Garant

Arbor for screw-in milling cutters with thread vibration-damped, tapered form, HSK-A 63, Thread M×length L1: M8X75



Order data

Order number	307037 M8X75
GTIN	4045197905031
Item class	31A

Description

Version:

With RFID/Balluffchip bore. Tapered design. **Vibration damped version, arbor with vibration-damping core.**

Application:

To take screw-in milling cutters with thread.

Optional extras:

Extensions No. 301342, reducers No. 301344, coolant tube No. 309880, coolant tube socket wrench No. 309890.

Note:

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

Technical description

Thread M	M8×75
Bore Ø D ₁	8.5 mm
Reach L ₁	75 mm
External Ø D	23 mm
Overhang dimension A	101 mm
L ₂	5 mm

Ø D ₂	13 mm
Adapter	HSK-A 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor